
Telstar | E25134-133NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Translucent acrylic panels dotted to guide indirect LED strips integrated into the body of the fixture. The angular forms of the pendants create a strikingly modern display of light that is both airy and voluminous. An additional LED GU10 bulb is recessed at the bottom of the fixture for additional functional light. Available in Satin Brass or Matte Black finishes.



MEASUREMENTS

DIMENSION	: 18" L x 18" W x 24" H
MAX OAH	: 67" OAH
CANOPY	: 4.75" W x 0.75" H x 4.75" L
HANGING WEIGHT	: 4.6 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 3,920 Rated (1,960 Del.)
BULB	: 4 x 10.5W LED LED , 49W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: ELV or Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Natural Aged Brass (NAB)

GLASS

Patterned Acrylic 133

MATERIAL

Steel + Aluminum+Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 15
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com