


Flush Rectangular Stamped Steel Floor Boxes, for Use In Concrete Floors

Style	Stamped Steel							
	1-Gang Deep	2-Gang Deep	3-Gang Deep	1-Gang Shallow	2-Gang Shallow	3-Gang Shallow	1-Gang Deep	1-Gang Shallow
								
Collar Material: Brass Aluminum	B2431* BA2431*	B2432 BA2432	B2433 BA2433	B2421* BA2421*	B2422 BA2422	B2423 BA2423	B2427* BA2427*	B2429* BA2429*
Min. Depth of Pour	3.75" (95.3)	3.75" (95.3)	3.75" (95.3)	2.75" (69.9)	2.75" (69.9)	2.75" (69.9)	4.00" (101.6)	3.00" (76.2)
Adjustability	Fully	Fully	Fully	Fully	Fully	Fully	Fully	Fully
Before Pour External Height Adjustment	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)
After Pour Internal Height Adjustment	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.38" (9.5)	.38" (9.5)
Cubic Inch (cm ³) Capacity per Gang	60.0 cu. in. (983.2 cm ³)	52.8 cu. in. (865.2 cm ³)	50.8 cu. in. (832.5 cm ³)	39.5 cu. in. (647.3 cm ³)	35.0 cu. in. (573.5 cm ³)	34.0 cu. in. (557.2 cm ³)	54.0 cu. in. (884.9 cm ³)	37.3 cu. in. (611.2 cm ³)
Dimensions – A	3.72" (94.5)	3.72" (94.5)	3.72" (94.5)	2.74" (69.6)	2.74" (69.6)	2.74" (69.6)	3.90" (99.1)	2.81" (71.4)
Dimensions – B	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	6.00" (152.4)	6.00" (152.4)
Dimensions – C	6.00" (152.4)	9.25" (235.0)	12.50" (317.5)	6.00" (152.4)	9.25" (235.0)	12.50" (317.5)	4.81" (122.2)	4.81" (122.2)
Dimensions – D	4.36" (110.7)	4.36" (110.7)	4.36" (110.7)	4.36" (110.7)	4.36" (110.7)	4.36" (110.7)	4.36" (110.7)	4.36" (110.7)
Dimensions – E	3.20" (81.3)	6.44" (163.6)	9.67" (245.6)	3.20" (81.3)	6.44" (163.6)	9.67" (245.6)	3.20" (81.3)	3.20" (81.3)
Knockouts – Sides	(1) ¼", (1) 1¼"	(2) ¼", (1) 1¼"	(3) ¼", (1) 1¼"	(2) ½", (1) ¾"	(4) ½", (2) ¾"	(6) ½", (6) ¾"	(1) ½", (1) 1¼"	(2) ½", (1) ¾"
Knockouts – Ends	(1) ¼", (1) 1¼"	(1) ¼", (1) 1¼"	(1) ¼", (1) 1¼"	(1) ½", (1) ¾"	(2) ½", (2) ¾"	(2) ½", (2) ¾"	(1) ¾", (1) 1"	(1) ½", (1) ¾"
Knockouts – Bottom	(2) ¼", (1) 1¼"	(4) ¼", (1) 1¼"	(6) ¼", (1) 1¼"	(2) ¾", (1) 1¼"	(4) ¾", (1) 1¼"	(6) ¾", (1) 1¼"	(3) ½", (2) ¾"	(3) ½", (2) ¾"
Concrete Cover Included	✓	✓	✓	✓	✓	✓	✓	✓
Closure Plugs Included	–	–	–	–	–	–	–	–
Removable LV Barrier	–	✓	✓	–	✓	✓	–	–

Note: UL File Number E92074.

CSA File Number LR18416.

*Suitable for single service applications only.

Carpet Flanges

Tapered Flange							
Number of Gangs	1-Gang		2-Gang		3-Gang		
Dimensions	6.00" x 4.85"		6.00" x 8.13"		6.00" x 11.34"		
Brass	SB3083		SB3084		SB3085		
Aluminum	SA3083		SA3084		SA3085		
Clear Polycarbonate	S3083		S3084		S3085		

Covers – One Required per Gang

Brass	S3825	S3625	S3826	S2425	S2625	S2825	S3813
Aluminum	SA3825	SA3625	SA3826	SA2425	SA2625	–	SA3813
Dimensions	4.15" x 2.99"						
							
	Duplex Flap	Duplex Screw	Style Line® Decorator Opening	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	Blank

Dimensions in Inches (mm)