

Leather glove, winter-lined, full grain goatskin of top quality, neoprene, Thinsulate™ 120g, Cat. II, reinforced fingers and thumb, waterproof, for allround work

TEGERA® DYNAMIC STRENGTH 7797

Learn more

Leather glove, winter-lined, full grain goatskin of top quality, neoprene, Thinsulate™ 120g, Cat. II, reinforced fingers and thumb, waterproof, for allround work

CHARACTERISTICS

- Good fingertip sensitivity
- Extra flexible
- Durable
- Perfect fit
- Good grip
- Extra comfortable
- Warm
- High level of protection

FUNCTIONS

- Reinforced index finger
- Reinforced fingertips
- Reinforced thumb
- Pre-curved fingers
- Specially designed thumb
- Waterproof
- Moisture resistant
- Reflector

Thinsulate™ INSULATION

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with moisture, Contact with damp, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Cold environments, Wet environments, Moist environments

PRIMARY AREAS OF USE

Airport work, Wood industry work, Forest work, Agricultural work, Gardening, Repair work, Fishing, Hunting, Decontamination, Sanitation, Machine driving, Warehouse work, Machine operating, Building and construction, Carpentry, HVAC installation, Construction, Soil preparation, Concrete work, Transport work

PRIMARY INDUSTRIES OF USE

Facility management services, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying, Warehousing, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Heavy duty gloves, Cold insulation gloves
CATEGORY Cat. II
COLLECTION Dynamic Strength
PALM MATERIAL Full grain goatskin of top quality
BACK MATERIAL Neoprene, Full grain goatskin of top quality
LINING Winter-lined
LINING MATERIAL Thinsulate™ 120g
LENGTH 260-280 mm
DEXTERITY 5
COLOUR Black
PAIRS PER: BUNDLE/CARTON 3/36
DISPLAY TYPE Hangtag with euro slot
FASTENING Hook-and-loop
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Polyester
MIDDLE MATERIAL SPECIFICATION Thermoplastic polyurethane (TPU)
OUTER MATERIAL SPECIFICATION Leather, Elastane, Polyester

COMPLIANCE

CE Cat. II
EN ISO 21420:2020
EAC TP TC 019:2011
EN 388:2016+A1:2018 2222X
EN 511:2006 211
ANSI 4 ABR

FEATURES

Warm lining
Waterproof
Windproof

SIZE		ARTICLE NUMBER	EAN
7	S	7797-7	7340118347578
8	M	7797-8	7340118347660
9	L	7797-9	7340118347752
10	XL	7797-10	7340118347844
11	XXL	7797-11	7340118347936
12	3XL	7797-12	7340118348025

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.