
Bevel | E42065-BBK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

White Acrylic diffusers are miter cut and beveled along the edge of these mirror frames allowing for wider, and brighter lighting. Robust in size, these mirrors feature excellent construction and 2CCT light selection using a discreet touch switch on the frames edge. Use the touch dimming switch to control the brightness and the memory function on the LED will recall the chosen color temperature of the previous setting.



MEASUREMENTS

DIMENSION	: 24" W x 36" H x 6.25" Ext
HANGING WEIGHT	: 45.32 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 4,000 Rated (1,500 Del.)
BULB	: 1 x 47W LED DC Integrated , 47W Total
BULB INCLUDED	: (Integrated)
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Brushed Black (BBK)

Satin Nickel (SN)

MATERIAL

Aluminum, PC, Glass

RATINGS

cETLus
Damp Location
CA Title 24

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com