



## 022-5294

### Northstar Coastal Edge 50' SS Cable SRL

#### FEATURES :

- Exclusive cable retraction limiter
- Simplified cable replacement system
- Semi-sealed mainspring
- Semi-sealed pawl assembly
- Oscillating, double-locking/anti-ratcheting pawls
- 360/180° swivel attachment point w/alu carabiner
- Lifeline handle w/ mini absorber and indicating stainless steel swivel snap hook
- RFID equipped for easy asset tracking
- All components are Z359.12 compliant

\*\*\*Eligible for service and repair\*\*\*

Class

# 2

Anchor above or below dorsal D-ring



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.14-2021
OSHA	1910.140, 1910.66

ANSI CLASS 1	
Max. arrest force	≤ 1,800 lbs. (817 kg)
Avg. arrest force	≤ 1,350 lbs. (612 kg)
Max. arrest distance	≤ 42 in. (107 cm)
Actual arrest distance	≤ 39 in. (99 cm)
Max. free fall distance	24 in. (61 cm)
Min. required fall clearance	6 ft. 9 in. (2 m)
For full clearance requirements, see user instructions	

ANSI CLASS 2	
Max. arrest force	≤ 1,800 lbs. (817 kg)
Avg. arrest force	≤ 1,350 lbs. (612 kg)
Max. arrest distance	N/A
Actual arrest distance	91 in. (231 cm)
Max. free fall distance	72 in. (183 cm)
Min. required fall clearance	16 ft. 1 in. (4.9 m)
For full clearance requirements, see user instructions	

MATERIAL SPECIFICATION	
Cable	13/64" stainless steel
Carabiner	Aluminum
Housing	Polycarbonate
Load-Indicating Swivel Snap Hook	Stainless steel
Shock pack	Polyester

