

# HOM120CAFIC

Mini circuit breaker, Homeline, 20A, 1 pole, 120 VAC, 10 kA AIR, combo arc fault, pigtail neutral, plug in mount



## Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A
Certifications	UL Listed
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Combination ARC-fault
Ratings	HACR rated
Electrical Connection	Clamp terminal for 2 cables
Wire Size	AWG 14...AWG 8 aluminium/copper)1 AWG 14...AWG 10 copper)2
Type of packing	Clam packaging

## Complementary

Connections - terminals	Pigtail neutral
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)
Tightening torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) AWG 14...AWG 8)

## Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	01321 - HOMELINE 1 POLE BULK BRK
Discount Schedule	CPH
GTIN	00785901477150
Nbr. of units in pkg.	1
Package weight(Lbs)	0.65 lb(US) (0.29 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.20 in (3.048 cm)
Package 1 width	4.50 in (11.43 cm)
Package 1 Length	7.90 in (20.066 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	3
Package 2 Weight	33.60 oz (952.543 g)
Package 2 Height	8.00 in (20.32 cm)

Package 2 width	3.90 in (9.906 cm)
Package 2 Length	4.70 in (11.938 cm)
Unit Type of Package 3	PAL
Number of Units in Package 3	960
Package 3 Weight	704.00 lb(US) (319.329 kg)
Package 3 Height	40.00 in (101.6 cm)
Package 3 width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	Lifetime
----------	----------