



Technical Data

Color	Black, Green
Sizes Available	OS-2XL
Packaging	Bagged Each
Packed	1/Case
Case Weight (lbs)	0.00
Country of Origin	Mexico
Certifications	TAA Compliant
Harness Points of Adjustment	5
Harness Style	H
Extended D-Ring	No
Coated	No
Harness Integrated Padding	Yes
Harness Integrated Chair	No
Harness Reflective Webbing	No
Webbing Material	Polyester
Harness Lumbar Support	Yes

Miller® H500

Industry Standard Full-Body Harness with 5 Points of Adjustment, Back/Front D-Rings, Mating Chest Buckles & Tongue Leg Buckles

- New specially formulated webbing flexes to accommodate movement and body contours for optimum comfort
- Detachable soft shoulder pads for added comfort
- Waist pad with adequate foam density for optimum lumbar support
- New ergonomically designed pressure-relief breathable shoulder/back padding keeps workers drier and cooler
- Smart anti-tangle design for a hassle-free donning experience
- Dedicated SRL web link for easy attachment of personal SRLs
- User-friendly resettable lanyard keepers allow users to attach lanyard when not in use
- Clearly identifiable smart impact indicators for hassle-free inspection
- Rated to 420 lb (max. weight capacity)
- Certified to OSHA 1926.502, ANSI Z359.11, and CSA Z259.10 standards
- This harness is ideal for industrial workers seeking safety, comfort, and ease of use during demanding tasks

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
H5IS31110S2	Black	OS	612230303068		
H5IS31110S1	Black	S/M	612230303051		
H5IS31110S3	Black	2XL	612230303075		
H5IS311102	Green	OS	612230242268		
H5IS311101	Green	S/M	612230242251		
H5IS311103	Green	2XL	612230242275		