Hoopla | E24327-WTGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Rings of various sizes finished in Black are supported from a column of soft Gold. This European classic is a soft contemporary design which works in today's home decor.



*max overall height

MEASUREMENTS

DIMENSION	: 37.5" L x 45.25" W x 16.25" H
MAX OAH	: 139" OAH
CANOPY	: 2.75" H x 10" L
HANGING WEIGHT	: 26.4 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 7,980 Rated (4,400 Del.)
BULB	: 1 x 114W LED PCB Integrated , 114W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 80+ CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black / Gold (BKGLD)

White/Gold (WTGLD)

MATERIAL

Steel, Aluminum, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

ADJUSTABLE
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com