



PIP® Kilimanjaro™

Type II Full Brim Hard Hat with HDPE Shell, 4-Point Textile Suspension and Wheel Ratchet Adjustment

- Lightweight HDPE shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- EPS foam liner provides front, rear and lateral protection from impact and penetration
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	Gold, Royal, Yellow, Navy, Black, Orange, Sky Blue, Gray, White, Hi-Vis Yellow, Dark Green, Hi-Vis Orange, Lime, Red, Pink
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	26.00 x 15.50 x 28.50
Case Weight (lbs)	15.98
Country of Origin	Canada
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type II
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP642R-11	Black	OS	620606001630	10616314423045	10620606001637
280-HP642R-04	Dark Green	OS	620606001562	10616314323253	10620606001560
280-HP642R-13	Gold	OS	620606751634	10620606751631	20620606751638
280-HP642R-09	Gray	OS	620606001616	10616314323253	10620606001613
280-HP642R-31	Hi-Vis Orange	OS	620606002392	10616314419055	10620606002399
280-HP642R-44	Hi-Vis Yellow	OS	620606002408	10616314423076	10620606002405
280-HP642R-45	Lime	OS	620606939223	10616314805667	20620606939227
280-HP642R-08	Navy	OS	620606001609	10616314323253	10620606001606
280-HP642R-03	Orange	OS	620606001555	10616314323284	10620606001552
280-HP642R-20	Pink	OS	620606002385	10616314805704	10620606002382
280-HP642R-15	Red	OS	620606001654	10616314323338	10620606001651
280-HP642R-17	Royal	OS	620606001661	10616314437400	10620606001668
280-HP642R-07	Sky Blue	OS	620606001593	10616314361644	10620606001590
280-HP642R-01	White	OS	620606001531	10616314323338	10620606001538
280-HP642R-02	Yellow	OS	620606001548	10616314323376	10620606001545