Souffle | E25050-TRC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Deep pans of cast concrete in a traditional scalloped edge house LED integrated light sources behind curved opal white acrylic diffusers. Reminisce in the classical forms that benefits from the organic texture of cast concrete to add character to the design. Inspired by ramekins, these delectable LED treats are available in Chalk White, Terra Cotta, and Grey.



MEASUREMENTS

DIMENSION	: 10.5" L x 10.5" W x 3.25" H
CANOPY	: 7.5" W x 0.75" H x 7.5" L
HANGING WEIGHT	: 3.97 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 740 Rated (680 Del.)
BULB	: 1 x 15W LED AC Integrated , 15W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Chaulk White (CHK)
- Gray (GY)
- Terra Cotta (TRC)

MATERIAL

Concrete, PC , Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com