

## USB-C to DisplayPort Adapter – Thunderbolt 3, 3840 x 2160 (4K x 2K) @ 60 Hz, White

MODEL NUMBER: U444-06N-DP4K6W



4K USB-C adapter connects a DisplayPort (DP) monitor to the USB-C or Thunderbolt 3 port on your MacBook or Chromebook.

### Features

#### USB-C to DP Adapter Connects a DP 4K Monitor to Your USB-C or Thunderbolt 3 Device

This USB to DisplayPort 4K adapter helps you transmit digital audio and 4K video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to a DisplayPort-enabled television, monitor or projector. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen, or streaming video in crystal-clear 4K.

#### Supports USB DisplayPort Alternate Mode for Transmitting Video Signals

With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

#### Transmits Crystal-Clear 4K DisplayPort Video and Digital Audio

To send digital audio and Ultra High Definition video to a 4K-ready DisplayPort television, projector or monitor, connect the DisplayPort port to the display using a DisplayPort cable (sold separately). The USB to DisplayPort 4K adapter supports video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as well as 24-bit Deep Color (8 bits per channel) and 7.1-channel surround sound.

#### Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

#### Ready to Use Right Out of the Package

The plug-and-play USB-C to DP adapter is specifically designed for use with the MacBook, Google Chromebook Pixel and all other laptops, tablets and devices equipped with a female USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. It's about half the size of a credit card, making it easy to carry in a pocket, briefcase or laptop bag for connecting on the go.

#### 3-Year Warranty

The U444-06N-DP4K6W is backed by a 3-year warranty, ensuring reliability and performance.

### Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

### Applications

- Play video from your laptop or PC on a DisplayPort monitor
- Give a video presentation at a meeting, training session or conference
- Multitask in two or more applications on multiple displays
- Add a second monitor to your laptop and make it your primary monitor
- Edit large documents on two different monitors

### System Requirements

- Source device with USB-C or Thunderbolt 3 output that supports USB DisplayPort Alternate Mode
- Display device with DisplayPort input

### Package Includes



- U444-06N-DP4K6W USB-C to DisplayPort Adapter – Thunderbolt 3, 3840 x 2160 (4K x 2K) @ 60 Hz, White
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332213341
INPUT	
Bus Powered	Yes
Product Length (in.)	6.00
PHYSICAL	
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	0.55 x 1.8 x 1.1
Unit Weight (lbs.)	0.04
Unit Weight (kg)	0.02
Material of Construction	Plastic, PVC
Color	White
Cable Outer Diameter (OD)	4.5mm
Cable Jacket Rating	VW-1
ENVIRONMENTAL	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	5% TO 90% RH, Non-Condensing
BTUs	0.61 BTU/Hr
Power Consumption (Watts)	0.18
CONNECTIONS	
Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
Max Supported Video Resolution	4K x 2K (3840 x 2160) @60Hz
Displayport Specification	1.3
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	7.1-Channel Surround Sound
Driver Required	No
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>