Folio | E30151-SAWT

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

The soft fold of a rigid aluminum frame provides a look suitable for both interior and exterior applications. Select from a sandy Black exterior with Gold interior or Satin Aluminum with a White interior.



MEASUREMENTS

DIMENSION	: 6.25" W x 9.75" H x 3.25" Ext
BACK PLATE	: 4.75" W x 4.75" H x 5" HCO
HANGING WEIGHT	: 2.4 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 700 Rated (450 Del.)
BULB	: 2 x 5W LED AC Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Directional

FINISHES OPTION

Black / Gold (BKGLD)

Satin Aluminum / White (SAWT)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com