



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**65-943** - 15/20/25 Watt; 3K/4K/5K CCT Selectable LED Small Adjustable Wall Pack; 120-277 Volt; Bronze Finish



### GENERAL

Company	NUVO
EA Height	4.92
EA Width	7.48
EA Length	9.06
Bulb Included	Integrated
Dimmable Text	0-10V Dimming
Extends (in)	8.08
Material	Die-cast Aluminum
Fixture Type	Wall Pack
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 4KV
Total Harmonic Distortion	9.70%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	Bronze
Amps	0.125-0.054/0.167-0.072/0.208-0.090A
Integrated Features	Integrated Photocell
IOT Enabled	No
Lens Finish	Opaque
Lens Material	Impact Resistant PC
Lensed	Yes
Photo Cell	Yes - Bypassable
Power Factor	>0.9
Indoor Outdoor	Outdoor
Product Technology	LED

### ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	65x95
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40C (-40F) to +40C (+104F)
HID Equivalent	70W-100W
Lumens	2193L-3669L
Volts	120V-277V
Watts	15W/20W/25W

### PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	Integrated LED

### ADDITIONAL INFO

Warranty	5-Years
----------	---------

### PACKAGING

UPC	045923410291
Case Cube	1.0003
Case Height	11.02
Case Length	15.94
Case Quantity	4
Case UPC	10045923410298
Case Weight	17.31
Case Width	9.84
EA Cube	0.193
EA Height	4.92
EA Length	9.06
EA Quantity	1
EA Weight	4.08
EA Width	7.48
Pack Type	Box
Web Height	3.84
Web Width	6.5

### COMPLIANCE

CA Prop 65	Lead
DLC ID	S-3RBQDR
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24 Compliant	No