

Product data sheet

Characteristics

QO220CP

Mini circuit breaker, QO, 20A, 2 pole,
120/240VAC, 10kA, plug in mount, consumer
pack



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate
Type of Packing	Consumer packaging

Complementary

Interrupt Rating	10 KA 120/240 V AC 50/60 Hz 10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.02...0.04 in ² (10...25 mm ²) (AWG 8...AWG 2)
Height	2.99 in (76 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.60 lb(US) (0.272 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	01341-QO 2 POLE BULK BRKRS15-60A
Discount Schedule	CPQ
GTIN	047569838026
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.30 in (8.38 cm)
Package 1 Width	1.50 in (3.81 cm)
Package 1 Length	3.10 in (7.87 cm)
Package 1 Weight	8.64 oz (244.94 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	3.30 in (8.382 cm)

Package 2 Width	3.10 in (7.874 cm)
Package 2 Length	7.70 in (19.558 cm)
Package 2 Weight	3.00 lb(US) (1.361 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	8.10 in (20.574 cm)
Package 3 Width	6.90 in (17.526 cm)
Package 3 Length	17.30 in (43.942 cm)
Package 3 Weight	30.00 lb(US) (13.608 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Halogen content performance	Halogen free product