PRODUCT INFORMATION PACKET

Model No: A277
Catalog No: A277
Round Outlet Permanent Split Capacitor Draft Inducer Blower, 120 Volts, Flange: No
Draft Inducer Blowers



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Voltage	120 V	Motor Type	Permanent Split Capacitor
Thermal Protection	Thermally	Speed	3300/2600 rpm
Current	0.60/0.36 A	Number of Speeds	2
Frequency	60 Hz	Phase	1
Ambient Temperature	40 °C	UL	Yes
Insulation Class	B	CSA	No

Technical Specifications

Blower Outlet Shape	Round	Motor Enclosure	Open
Blower Outlet Flange	No	Bearing Type	Ball

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021