THE SNAPPY ADVANTAGE

Snappy is a leading manufacturer of forced air fittings with manufacturing locations in Minnesota, Colorado and Oregon. Snappy provides the highest quality product and very best delivery with virtually no back orders. Our products conform to the standard sheet metal size and gauge specifications.

PRODUCT ADVANTAGES:

PLENUMS – Snappy offers two styles: the #99 made to the customers exact specifications or the #99U made in many standard width and height combinations.

RETURN AIR DROPS AND FILTER RACKS – Snappy manufactures a number of drops, support boxes and filter racks; many additional sizes are also available.

RECTANGULAR DUCT – Snappy manufactures all standard rectangular duct dimensions in 4', 5' and 8' lengths. All duct sizes and lengths are produced on the Snappy revolutionary Automatic Duct Line, insuring the highest quality duct available in todays industry.

RECTANGULAR DUCT FITTINGS – Die punched parts and riveted construction make Snappy duct fittings the best in the market.

ROUND TO ROUND AND RECTANGULAR TO ROUND TAKEOFFS – Machine produced components and die punched parts make Snappy takeoffs size consistent with dependable high quality. Snappy S-5 and T-5 have a patented base section for speed and ease of installation.

PIPE AND ELBOWS – All the Snappy pipe is manufactured on coil fed, highly automated lines providing a consistent size and snap-lock. Elbows are produced on the Snappy Automatic Elbow Machines, ensuring high quality, ease of adjustment and perfect sizing.

PERIMETER BOOTS, STACK BOOTS, REGISTER AND CEILING HEADS – Die punched parts, consistent quality and size, riveted construction, air tight with hemmed collars.



PVC FITTINGS – PVC coated 26 GA steel, 3 mil thickness on the outside and 1 mil on the inside. All fittings manufactured to the same Snappy standards for high quality and consistent sizing. All applicable fittings shipped with styrofoam inserts for poured cement installations.




OVAL PIPE AND FITTINGS – The most economical system for second story installations. The finest in the industry. The boots are made to fit within the floor joists and not hang below.

BLACK-TITE PIPE AND FITTINGS – Made on Snappy automated equipment using a mill-finish, scratch resistant steel, producing the most aesthetic product in the wood heat industry.









MAY-AIRE FRESH AIR EXCHANGER - A compact, lightweight, highly efficient unit designed for easy installation and years of trouble free service.

DUCT AND FITTINGS

Number and Item	Size	Ctn.
 28 ga 26 ga. No. 100 4', 5' and 8' Duct	8 x 8 10 x 8 12 x 8 14 x 8 16 x 8 18 x 8 20 x 8 22 x 8 24 x 8 26 x 8 30 x 8 4' Duct 5' Duct 8' Duct	6 Jts. 5 Jts. As Ordered
 No. 50 Offset Starting Collar 2" Rise No. 45 Straight Starting Collar	8 x 8 10 x 8 12 x 8 14 x 8 16 x 8 18 x 8 20 x 8 22 x 8 24 x 8 26 x 8 30 x 8	6 6 6 6 6 6 6 6 6 As Ordered

	Duct Size	Plenum Size 46L & 48R	Plenum Size 47C	Ctn Qty.
 No. 46L Transition	14 x 8 16 x 8 18 x 8 20 x 8 22 x 8 24 x 8 26 x 8 30 x 8	12 x 10 13 x 10 15 x 10 16 x 10 18 x 10 16 x 12 15 x 14 18 x 14	12 x 10 13 x 10 15 x 10 18 x 10 18 x 10 20 x 10 22 x 10 24 x 12	3 3 3 3 3 3 3 3
 No. 47C Transition 2" Rise				
 No. 48R Transition				

	Size	Ctn.
 No. FR Filter Rack	14 x 20 16 x 20 16 x 25 20 x 20 20 x 25	12 12 12 12 12

Number and Item	Size	Ctn. 190	Ctn. 109
 No. 190 90˚ B.W. Elbow Radius=2" x 2"  No. 109 45˚ B.W. Angle	8 x 8 10 x 8 12 x 8 14 x 8 16 x 8 18 x 8 20 x 8 22 x 8 24 x 8 26 x 8 30 x 8	6 6 6 3 3 3 3 3 3 As Ordered	6 6 6 6 6 6 6 6 6 As Ordered
 No. 116 90˚ S.W. Elbow Radius=2" x 2"  No. 106 45˚ S.W. Angle  No. 113 Reducer (State Sizes)	8 x 8 10 x 8 12 x 8 14 x 8 16 x 8 18 x 8 20 x 8 22 x 8 24 x 8 26 x 8 30 x 8	116 6 6 6 6 6 6 6 3 3 As Ordered	106 6 6 6 6 6 6 6 6 6 As Ordered 113 As Ordered
 No. 212 Duct End Cap  No. 212FSD (For Slip & Drive)	8 x 8 10 x 8 12 x 8 14 x 8 16 x 8 18 x 8 20 x 8 22 x 8 24 x 8 26 x 8 30 x 8	12 12 12 12 12 12 12 12 12 12 12	
 No. 49 Duct Reducer	2 x 8 4 x 8 6 x 8 8 x 8	12 12 12 12	
 No. 49S Duct Reducer	2 x 8 4 x 8 6 x 8 8 x 8	12 12 12 12	