



PIP® Mega T-Fit™

T-Shape Disposable Soft Polyurethane Foam Ear Plugs - Dispenser Refill Pack

- 250 pairs of 267-HPF510 disposable ear plugs loose in display box
- Consistent cellular structure for optimal expansion recovery time for a custom, uniform fit
- Smooth closed cell outer layer that prevents debris build-up
- Soft and comfortable PowerSoft™ foam supports all day comfort
- NRR 32 protection

Technical Data

Color	Orange
Sizes Available	OS
Packaging	Bulk Pack
Packed	20 Boxes/Case
Case Dimensions (in)	18.37 x 19.37 x 9.06
Case Weight (lbs)	15.72
Country of Origin	Mexico
Hearing Style	Uncorded
Ear Plug Material	Polyurethane Foam
Shape	T-Shape
Box Count	250
Certifications	TAA Compliant

Performance Data

NRR Rating (ANSI S3.19-1974)	32
SNR Rating	37
SLC 80	22
SLC 80 Class	Class 4

Care Instructions

These ear plugs are disposable, but when not in use should be kept in clean, dry condition.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
267-HPF510-1	Orange	OS	616314396892	10616314429740	20616314396896