Syndicate | E21380-18BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Segmented by bright LED rings finished in Matte Black, glass shades of an hourglass shape are combined into various configurations. The hand-blown glass is entirely transparent and varies in size creating an undulating pattern. All together, the series includes pendants, flush mounts, and portable lamps.



MEASUREMENTS

DIMENSION	: 8.75" L x 8.75" W x 11.25" H
CANOPY	: 6.75" W x 1.5" H x 6.75" L
HANGING WEIGHT	: 7.93656 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 960 Rated (720 Del.)
BULB	: 2 x 9W LED DC Integrated , 18W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

GLASS

Clear 18

MATERIAL

Aluminum,Steel,Glass

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com