

Project Name

Location

Prepared By



SATCO S4160

40A15 CLEAR E12 NICKEL PLATED

Notes

[www] 06-27-2021 00:19:12

General

Status	Active
Watts	40W
Volts	130V
Shape	A15
Filament	C-9
Base	Candelabra
ANSI Base	E12
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	100
Lumens	420L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	1000
Lamp Type	Type A
Technology	Incandescent

Physical

MOL	3.38
MOD	1.88

Additional Information

Warranty	Avg. Rated Hour Limited
----------	-------------------------

Compliance

Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	Incandescent_Lamp