



WLL03IP



3.75" x 24" x 20" (H x W x D)

24" wide off-grid propane gas cooktop in white with 4 open burners and battery start ignition, made in the USA

Highlights:

- Premium cast iron grates hold up to heavy duty cookware
- LP gas cooktop made in the USA and ideal for off-grid living
- Battery start ignition is ideal for locations without standard electrical power access

Product Features:

24" Wide Off-Grid Gas Cooktop	Battery-start propane cooktop ideal for rural areas
Made in the USA	Designed and constructed domestically
LP/propane cooktop	Ships pre-set for use with LP gas
Battery start ignition	Uses a 9V battery (included) to ignite the burners, providing a convenient off-grid solution to kitchens previously using pilot lights when no electricity is available
Cast iron grates	Two sets of continuous grates in heavy duty cast iron hold up to large cookware
Classic 24" size	Fits common 22 5/8" W x 18 5/8" D counter cutouts
Four open burners	9000 BTU burners to meet most cooking needs
White exterior	Classic design in a clean white finish to match any kitchen
Porcelain finish	Scratch-resistant design for lasting durability



WLL03IP Specifications:

Overview	
Nominal Height	4.0" (10 cm)
Height of Cabinet	3.75" (10 cm)
Nominal Width	24.0" (61 cm)
Width	24.0" (61 cm)
Nominal Depth	20.0" (51 cm)
Depth	20.0" (51 cm)
Cabinet	White
US Electrical Safety	CSA
Weight	27.0 lbs. (12 kg)
Parts & Labor Warranty	1 Year
UPC	761101161488
Gas Cooktop	
Ignition	Battery Start
LP Convertible	Pre-set for LP
Number of Burners	4
Controls	Dial
Surface	Painted
Grate Material	Cast Iron
Cutout Width	22.63" (57 cm)
Cutout Depth	18.63" (47 cm)
Burner #1 BTU	9000.0
Burner #2 BTU	9000.0
Burner #3 BTU	9000.0
Burner #4 BTU	9000.0
Power Cord Included	No

