

Popular for good reason.

Halogen lamps come in more sizes, shapes, and base variations than most other technologies, and with good reason – brilliant white light, great color temperature, and color rendering properties, long life, and superior lumen maintenance combine to make them very popular. Satco stocks virtually every variation there is. Our wide inventory allows you to get the types you need, whether a specialty size or an incandescent A19 replacement, that meets government regulations. When it comes to Halogen lamps, we can confidently say “Yes, we have that.”

Halogen lamp features:


- Available from 5 to 1500 Watts
- From 6 to 240 Volt variations
- All industry standard sizes and bases
- Fully dimmable
- Environmentally friendly – Mercury free
- Energy efficient
- Our Halogen Excel line saves up to 30% in energy costs over traditional incandescent lamps
- Halogen/Xenon technology for enhanced performance in our Halogen Excel™ line
- Excellent color rendering
- High lumen output




Nuvo Lighting's Lynne five light vanity in Polished Nickel with Frosted Glass. Nuvo item number 60-5178. See the www.nuvolighting.com website.



HALOGEN



T4 G8
Wide Pin



T4
GY6.35



T3.5
G6.35c

Bi Pin Lamps 120 Volt

Watts	Bulb Type	Base	Satco Prod. #	Lamp Code	Volts	Finish	M.O.L. Inches	Filament	Initial Lumens	Avg. Rated Hours	Pkg. Type	Master/ Inner Carton	Notes
20	T4	G8	S4610	20T4/CL/G8	120	Clear	1 13/16	CC-2V	180	2000	Box	48	
			S3539	20T4/CL/G8	120	Clear	1 13/16	CC-2V	180	2000	CD/1	240/12	
25	T4	GY6.35	S3197	25T4/CL	120	Clear	1 15/16	CC-2V	210	2000	Box	48	
		G8	S4611	25T4/CL/G8	120	Clear	1 13/16	CC-2V	210	2000	Box	48	
35	T4	GY6.35	S3164	35T4/CL	120	Clear	1 15/16	CC-2V	380	2000	Box	48	
			S3418	35T4/CL	120	Clear	1 15/16	CC-2V	380	2000	CD/1	12	
		G8	S4620	35T4/CL/G8	120	Clear	1 13/16	CC-2V	380	2000	Box	48	
50	T4	GY6.35	S3167	50T4/CL	120	Clear	1 15/16	CC-2V	750	2000	Box	48	
			S3427	50T4/CL	120	Clear	1 15/16	CC-2V	750	2000	CD/1	12	
		G8	S4612	50T4/CL/G8	120	Clear	1 13/16	CC-2V	750	2000	Box	48	
75	T4	GY6.35	S3168	75T4/CL	120	Clear	2 3/8	CC-2V	750	2000	Box	48	
			S3428	75T4/CL	120	Clear	2 3/8	CC-2V	1250	2000	CD/1	12	
		G8	S4613	75T4/CL/G8	120	Clear	2 1/4	CC-8	1250	2000	Box	48	
100	T4	GY6.35	S1924	100T4/CL	120	Clear	2 3/8	CC-2V	1700	2000	Box	48	
			S3419	100T4/CL	120	Clear	2 3/8	CC-2V	1700	2000	CD/1	12	
		G8	S4622	100T4/CL/G8	120	Clear	2 1/4	CC-8	1700	2000	Box	48	
			S3543	100T4/CL/G8	120	Clear	2 1/4	CC-8	1700	2000	CD/1	12	

Bi Pin Marine Lamps 12 and 24 Volt

Watts	Bulb Type	Base	Satco Prod. #	Lamp Code	Volts	Finish	M.O.L. Inches	Filament	Avg. Rated Hours	Pkg. Type	Master/ Inner Carton	Notes
55	T3.5	GY6.35	S7183	JCD/12V/55W/DX	12	Clear	1 3/4	C-6	100	Box	500/10	ACR6001
			S7184	JCD/24V/55W/DX	24	Clear	1 11/16	C-6	100	Box	500/10	ACR6003