



Cut

Abrasion Protection



Medium Duty

Versatile industrial gloves, combining cut protection, advanced durability and dexterity

- **Heightened protection:** HyFlex® 11-644 cut-resistant gloves' INTERCEPT™ Cut Resistance Technology helps them achieve EN ISO B/ANSI A2 laceration defenses
- **Enhanced durability:** These abrasion-resistant gloves' polyurethane coating remains both maneuverable and hard-wearing over time
- **Improved ergonomics:** The 11-644 model's ergonomic fit and low palm weight makes it perfectly comfortable for highly precise operations
- **Genuine practicality:** HyFlex® 11-644 PPE gloves are also sold in vend pack form, for practical replenishment and re-application in real-world conditions



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

Applications

- Press shop operations
- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Seizing structural and body parts
- Inspection (picking, checking and marking)
- Feeding the press and removing spare parts from it
- Cutting glasses, sheets, panels

Key Features

- **INTERCEPT™ Cut Resistance Technology:** Preventing workplace injuries
- **Abrasion resistance:** Durable personal protection over long periods
- **Lightweight ergonomic fit:** Offering dexterity and all-day comfort

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-644	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: HPPE, Nylon, Spandex Cuff Style: Knitwrist	13	5, 6, 7, 8, 9, 10, 11, 12	207-277 mm; 8.14-10.90 inches	Grey	<ul style="list-style-type: none"> • 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3, 678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551