

# SAMANTHA

H1094101-AGB

A love affair with vintage decadence, the Samantha family features an expressive rise-and-fall chandelier and a botanically-inspired sconce. The swooping metalwork and central finial of the 3-light chandelier recall the sculptural curves of Art Nouveau. Soft cotton shade: gather at the bottom and relax at the top, creating a natural, fluted silhouette. An Aged Brass frame shimmers as you walk by.

## FINISHES

### AGED BRASS

Coastal Suitable Finish (EPM): No

## DIMENSIONS

Height: 14.5"

Width/Diameter: 5"

Length: 6.75"

Canopy/Backplate: 4.75"

Product Weight: 2lb

Extension: 6.75"

Top to Center: 8.25"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

## Shade

Shade 1: Textile

Shade 1 Finish: Natural Cotton Sateen

Shade 1 Top Width: 5"

Shade 1 Height: 6"

## ELECTRICAL



### Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

## SHIPPING

Carton 1: 14" x 10" x 11"

Carton 1 Weight: 3lb

Shipping Method: Ground

Country of Origin: VN

