



FF1514SSIM



67.75" x 27.5" x 26.25" (H x W x D)

Counter depth top-mount refrigerator-freezer with stainless steel doors and factory-installed icemaker

Highlights:

- Full-size capacity in a unique counter depth fit
- True frost-free operation saves you maintenance by preventing icy buildup
- Stainless steel doors and platinum cabinet bring a professional look to small kitchens

Product Features:

Counter Depth Refrigerator-Freezer	Top mount design in an efficient 27.5" W x 26.25" D footprint ideal for space-challenged kitchens
Stainless steel doors	Attractive look with lasting durability
Designer handles	Brushed steel handles offer a modern look for the refrigerator
Frost-free operation	No-frost convenience for reduced user maintenance
Factory installed icemaker	Keep a constant supply of ice cubes on hand inside the freezer
Large capacity	Generous capacity inside a counter deep footprint
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Crisper drawer	Get the longest life and best taste out of produce by storing it in a convenient slide drawer
Gallon door shelf	Deeper rack included to accommodate full gallon containers



FF1514SSIM Specifications:

Overview	
Nominal Height	68.0" (173 cm)
Height of Cabinet	67.25" (171 cm)
Height to Hinge Cap	67.75" (172 cm)
Nominal Width	28.0" (71 cm)
Width	27.5" (70 cm)
Width with Door Open	28.5" (72 cm)
Nominal Depth	27.0" (69 cm)
Depth	26.25" (67 cm)
Depth with Handle	27.75" (70 cm)
Depth with door at 90°	51.38" (131 cm)
Capacity	13.6 cu.ft. (385 L)
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Platinum
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	426.0kWh/year
Amps	2.4
Voltage/Frequency	115 V AC/60 Hz
Weight	185.0 lbs. (84 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101078816
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Interior Light	Yes
Refrigerator - Interior Height	39.0" (99 cm)
Refrigerator - Interior Width	23.5" (60 cm)
Refrigerator - Interior Depth	17.0" (43 cm)
Refrigerator - Capacity	10.1 cu.ft
Refrigerator - Shelf Type	Glass

Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	19.0" (48 cm)
Freezer - Interior Width	22.25" (57 cm)
Freezer - Interior Depth	19.25" (49 cm)
Freezer - Capacity	3.23 cu.ft
Freezer - Shelf Type	Glass
Freezer - Shelf Qty	1
Freezer - Full Door Shelves	2
Gallon Door Storage	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	2.26 oz.
Level Legs	2
Compressor Step Height	10.0" (25 cm)
Compressor Step Width	23.5" (60 cm)
Compressor Step Depth	5.5" (14 cm)
Sound Level	32.9 dB

