Dram | E30193-93BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Dual Cylinder glass shades diffuse LED light bulbs concealed within rounded caps in Black powder coat. The single sconce is wet located with intention to be used outdoors, while the complementary 3-Light wall sconce is perfect for use in transitional to more modern bathrooms. The LED lamp provided is T24 JA8 compliant and Energy Star listed.



MEASUREMENTS

DIMENSION	: 22" W x 8.75" H x 6" Ext
BACK PLATE	: 4.75" W x 4.75" H x 2.5" HCO
HANGING WEIGHT	: 7 lb

LAMPING

INPUT VOLTAGE	: 120V
BULB	: 3 x 7W LED GU10 , 21W Total
BULB INCLUDED	: (Included)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)

GLASS

Clear and Frosted 93

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com