



Project / Job Name:

Location:

Fixture Type:

Notes:

S14385 - 8 Watt LED A19; Straight Filament; Orange Light; Glass; 120 Volt; 1-Pack



GENERAL

Company	SATCO
EA Height	4.92
EA Width	2.68
EA Length	2.68
Lamp Filament	Straight
Material	Glass
Fixture Type	Miniature
Status	Active
Surge Protection	Built-in-surge protection - 0.5KV
Total Harmonic Distortion	<150%
CCT Selectable	No
Wattage Selectable	No
Finish Family	Clear
Amps	0.105A
IOT Enabled	No
Lens Finish	Clear
Lens Material	Glass
Lensed	Yes
Operating Position	Universal
Power Factor	>0.5
SDS Class	LED_Lamp
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	60W

ELECTRICAL

Dimmable	Non-Dimmable
Hours Rated	15000
Beam Angle (degree)	330
Color Temp	Orange
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	800L
Volts	120v
Watts	8W

PHYSICAL

Lamp Base	Medium
Finish	Clear
ANSI Base	E26
Lamp Type	A19
MOD Lamps	2.36
MOL	4.29

ADDITIONAL INFO

Warranty	2-Years
Rated For Enclosed Fixture	Yes

FEATURES

Flicker Free	Yes
--------------	-----

PACKAGING

UPC	045923143854
Case Cube	0.7358
Case Height	11.57
Case Length	12.13
Case Quantity	24
Case UPC	10045923143851
Case Weight	3.52
Case Width	9.06
EA Cube	0.0204
EA Height	4.92
EA Length	2.68
EA Quantity	1
EA Weight	0.1
EA Width	2.68
Inner Cube	0.1469
Inner Height	5.31
Inner Length	8.43
Inner Quantity	6
Inner UPC	20045923143858
Inner Weight	0.69
Inner Width	5.67
Pack Type	Color Box
Web Length	4.29
Web Width	2.36

COMPLIANCE

ADA Compliant	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No