Project / Job Name:

Location:

Fixture Type:

Notes:



60-7368 - Bayard Swing Arm Lamp; Polished Nickel with Switch; Polished Nickel Finish

120 VOLT

GENERAL

Company	NUVO
EA Height	9.5
EA Width	14.0
EA Length	15.5
Bulb Included	No
Extends (in)	25.25
Shade Finish	Polished Nickel outside, Painted white inside
Material	Steel
Fixture Type	Sconce
Switch Type Name	Rotary
Includes	(1) 6 Inch and (1) 12 Inch rod; All hardware to convert to a portable OR to convert to Direct Wire
Status	Active
Rod Length	18.0
Style	Modern Industrial
Wire Color	Clear
Wire Length	72.0
CCT Selectable	No
Collection	Bayard
Finish Family	Nickel
Additional Info	Convertible Plug In or Direct Wire Option; Ceramic Socket; Rotary On/Off Switch with Decorative Metal Cap; Adjustment points at lamp head, arm joint, and wall plate.
Amps	0.500A
Mounting Diameter	4.75
Has Camera	No
IOT Enabled	No
Photo Cell	No
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	Lamp Dependent
Fixture Lamp Count	1
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

Dimmable	Non-Dimmable
Volts	120v
Watts	60W
Connection	Convertible or Hardwired

PHYSICAL

Lamp Base	Medium
Finish	Polished Nickel
ANSI Base	E26
Lamp Type	A19
Mounting Procedure	Ceiling/Wall

ADDITIONAL INFO

Warranty	1-Year

FEATURES

Flicker Free	No

PACKAGING

UPC	045923671197
Case Cube	1.193
Case Height	9.5
Case Length	15.5
Case Quantity	1
Case UPC	10045923671194
Case Weight	4.91
Case Width	14.0
EA Cube	1.193
EA Height	9.5
EA Length	15.5
EA Quantity	1
EA Weight	4.91
EA Width	14.0
Pack Type	Box
Web Height	13.38
Web Width	8.0

COMPLIANCE

ADA Compliant	No
Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
IC Rated	No
Location Rating	Dry
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
DLC Approved	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026