Diaphane | E11030-95GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION

Hexagonal tubes of various lengths support blocks of naturally translucent rock crystal. Each stone varies in diaphaneity making a unique display of refracted light. Available in a plated soft Gold or Matte Black, this luxurious LED pendant light cluster and coordinating wall sconce accentuates the beauty of the natural quartz material.

MEASUREMENTS

DIMENSION	: 4.75" W x 15.75" H x 4.5" Ext
MAX OAH	: 4.75" W x 4.75" H
HANGING WEIGHT	: 2.4 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 400 Rated (240 Del.)
BULB	: 1 x 5W LED PCB Integrated , 5W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)

Gold (GLD)

GLASS

Rock Crystal 95

MATERIAL

Steel, Aluminum, Rock Crystal

RATINGS

cETLus
Damp Location

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com