



North® Butyl™ 13 Mil Butyl Rubber Glove with Smooth Grip - 11"

- Exceptional resistance to a broad range of toxic chemicals: making it the only suitable for many critical applications
- Highly resistant to ketones (MEK: MIBK: acetone) and esters (tricresyl phosphate: amyl acetate: ethyl acetate)
- Solvent based: multi-dip manufacturing process provides multiple layers of polymer (like a glove within a glove) which results in a glove of superior quality
- Butyl provides the highest permeation resistance to vapors and gases



Technical Data

Color	Black
Sizes Available	S-2XL
Polymer	Butyl
Thickness	13 Mil
Lining	Unlined
Dip	Single
Length	11"
Cuff	Rolled
Grip	Smooth
Construction	Unsupported, Waterproof
Case Dimensions (in)	32.00 x 21.00 x 15.00
Case Weight (lbs)	60.01
Packed	288 Pair/Case
Packaging	Bagged Pair
Certifications	TAA Compliant, Latex Free
Country of Origin	United States

Performance Data

EN 374-5	Bacteria and Fungi
----------	--------------------

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
B131/7	Black	S	821812007762	821812007755	00821812007748
B131/8	Black	M	821812007793	821812007786	00821812007779
B131/9	Black	L	821812007823	821812007816	00821812007809
B131/10	Black	XL	821812007700	821812007694	00821812007687
B131/11	Black	2XL	821812007731	821812007724	00821812007717