SIEMENS

## Data sheet US2:PN2040L1200C

SIEMENS LOW VOLTAGE PLUG-ON NEUTRAL READY PRO SERIES ASSEMBLED LOAD CENTER. MAIN LUG WITH 20 1-INCH SPACES ALLOWING MAX 40 CIRCUITS. 1-PHASE 3-WIRE SYSTEM RATED 120/240V (200A) 100KAIC. SPECIAL FEATURES: COPPER BUS, GREY TRIM NEMA TYPE 1 ENCLOSURE FOR INDOOR USE.

| | |
|---|---|
| **General technical data** | |
| configuration of the busbars | COPPER BUS |
| number of circuits in a trunking unit | 40 |
| phase number | 1 |
| suitability for operation | RESIDENTIAL AND LIGHT COMMERCIAL ELECTRIC DISTRIBUTION |
| **Electricity** | |
| ampacity | 200 A |
| voltage between phase and Ground (GND) rated value | 120 V |
| voltage between phase and phase rated value | 240 V |
| **Model** | |
| product brand name | SIEMENS |
| product sub brand name | LOAD CENTERS |
| product type designation | PLUG-ON NEUTRAL READY PRO SERIES |
| special product feature | GREY TRIM |
| **Mechanical Design** | |
| number of modular width units for installation width | 20 |
| **General product approval** | |
| certificate of suitability | UL |

**last modified:** 7/9/2021


Subject to change without notice
© Copyright Siemens