Pasha | E21432-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Pasha combines architectural lines with regal inspiration. Thin Trapezoid shades function as elevated task lighting or picture lighting. The arm from the back plate to the light source is extendable allowing you to position the strip of light housed in the metal shade closer or further in position while a pivoting gimbal at its joint allows you to rotate the light and direct its beam. Available in Gold and Black, these picture lights coordinate with many interior color schemes.



MEASUREMENTS

DIMENSION	: 23" L x 12" W x 5.5" H x 12" Ext
MAX OAH	: 5.5" W x 4.75" H
HANGING WEIGHT	: 0.8 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,520 Rated (1,200 Del.)
BULB	: 1 x 19W LED DC Integrated , 19W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black (BK)
Gold (GLD)

MATERIAL

Aluminum

RATINGS

cETLus
Dry Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com