



TEGERA® 12

Learn more

DURABLE GLOVE WITH GOOD DEXTERITY

Versatile leather glove for assembly work and general handling tasks. The goatskin leather offers good dexterity and grip, making it easy to handle parts and tools. A breathable cotton back helps keep hands comfortable during work. Reinforced fingertips add durability in areas exposed to wear. A flexible design and good fit make this a practical choice for everyday tasks.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Good fit

FUNCTIONS

- Reinforced fingertips

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Dry environments, Clean environments, Dirty environments

PRIMARY AREAS OF USE

Assembly, Machine operating, Building and construction, Carpentry, Installation work, Tiling, Construction, Warehouse work, Gardening, Repair work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Agriculture, forestry and fishing, Facility management services, Rubber and plastics manufacturing, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying, Warehousing, Pulp and paper, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Light weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves
CATEGORY Cat. II
PALM MATERIAL Full grain goatskin
BACK MATERIAL Cotton
LENGTH 225-270 mm
DEXTERITY 5
COLOUR Blue
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Thread
FASTENING Elasticated 180°
OUTER MATERIAL SPECIFICATION Leather, Cotton

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018
2011X

ANSI 3 ABR

SIZE		ARTICLE NUMBER	EAN
7	S	12-7	7392626035454
8	M	12-8	7392626035461
9	L	12-9	7392626035478
10	XL	12-10	7392626035485
11	XXL	12-11	7392626035492

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.