

RoHS COMPLIANT

REVISION INFORMATION

Rev.	Rev. Date	Brief Description

End A

End B

Length

1

2

2

Length Tolerance:
+50mm/-0(Length<1M);
+100mm/-0(1M≤Length≤10M);
+1%/-0(Length>10M).

Performance:

1. Insertion Loss: ≤0.35dB.
2. Return Loss: ≥26dB.
3. Polarity: Type B

PID	Description
48219	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 1m
48220	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 2m
48221	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 3m
48222	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 5m
48223	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 10m
48224	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 15m
48225	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 20m
48226	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 25m
48227	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua 30m

MONOPRICE

DESCRIPTION :

Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 Elite UPC Female to MTP®-12 Elite UPC Female 12-Fiber OFNP Type B Aqua

PID # :

48219 - 48227

DATE :

UNIT : M / MM

FILE NAME:

2	12C MTP/UPC Female Elite MM Connector / Aqua Housing; Black Boot	2		
1	OD:3.0mm, Multimode 50/125 OM4, Elite, 12F, Fiber Optic Cable OFNP Color: Aqua	1		
NO.	PART NAME	SPECIFICATION DESCRIPTION	QTY	UNIT