







Slide Changeable Glassboard

Questions? Give us a call! 800-543-0550



Included in box:

Quantity	Item Description	Image
1	Glassboard	
4	Wall Anchors (1/4" drill bit required)	
4	#6 x 2" Screw (1/16" drill bit required)	
4	Threaded Brass Washer	
4	Stand-off Caps	
4	Steel Washer	
4	Nylon Washer	
1	VividCore Insert	
4	2mm Hex Key	

Tools Needed:

- Tape measure
- Level
- Drill
- Stud finder
- 1/16" Drill bit
- 1/4" Drill bit
- #2 Phillips head driver bit
- Masking tape
- Pen / Marker
- Hammer

Installation Instructions:



We recommend having two people install each Slide Changeable board to insure a level installation.

1. Align the glassboard onto the template and mark all four hole locations with a pen/marker.
2. Position and level the template onto the wall at the desired location, finding studs if possible using a stud finder. Use masking tape to hold the template in place.
3. Pre-drill at the marked hole locations. If hitting a stud use a 1/16" drill bit at all hole locations. If not hitting studs use a 1/4" drill bit at all hole locations.
4. Remove the template from the wall.
5. If you did not hit studs insert the included wall anchors
6. Clean both sides of the glassboard.
7. Align the glassboard on the wall. Insert the nylon washer, steel washer, threaded brass and screw.
8. Screw the stand-off caps onto each threaded washer to secure the board to the wall.
9. To make caps tamper resistant, use the included hex key to tighten the set screw on the side.
10. Slide the VividCore insert behind the glass.

