Groove WiZ | E22720-GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








Connected by WiZ

PRODUCT DESCRIPTION

Groove 5CCT brings clean geometry and modern versatility to everyday lighting. Formed from a slim aluminum channel, each integrated LED ring creates a refined halo of light with a recessed downlight for a crisp, architectural effect. Offered in Matte Black or Brushed Gold, the collection spans a wide range of diameters from 24", 32", and 40" to dramatic new 60" and 72" sizes. A coordinating 24" flush mount extends the look to lower ceilings. Five selectable color temperatures, from warm 2700K to bright 5000K, allow the light to adapt to each space.



MEASUREMENTS

DIMENSION	: 24.5" L x 24.5" W x 3.25" H
CANOPY	: 24.5" W x 1.25" H x 24.5" L
HANGING WEIGHT	: 8.8 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,000 Rated (1,250 Del.)
BULB	: 1 x 27W LED PCB Integrated , 27W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Dimmable W/ WIZ compatible device or app
CRI	: 90 CRI
COLOR_TEMP	: 2700-6500K

FINISHES OPTION

Black (BK)
Gold (GLD)

MATERIAL

Aluminum + Acrylic

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com