

HOPKINS

PTL4828-PBR

The artful Indian cut glass techniques and dramatic ombre of Hopkins create a truly striking table lamp. The cylindrical glass base has a fine, textural quality, accented by artistic etchings. A rich gray-blue hue deepens into a darker shade at the base, creating a moody gradation. To let the beauty of the base shine, Hopkins is topped with a simple white linen taper shade.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 28"

Width/Diameter: 17"

Canopy/Backplate: 6"

Product Weight: 11lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Fabric

Shade 1 Finish: Off White Linen

Shade 1 Top Width: 15.5"

Shade 1 Bottom L/W: 0" / 17"

Shade 1 Height: 10"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Bulb Included: No

Cord Type: SPT-2 BLACK FABRIC

Switch Type: ON/OFF SWITCH ON SOCKET

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 27" x 16" x 33"

Carton 1 Weight: 23lb

Shipping Method: Ground

Country of Origin: IN

