
MASTER
THE PROFESSIONAL'S CHOICE SINCE 1953


Master MAC-18WW - 18" 3-Speed Circulation Fan with Mount 3040 CFM, 1/6 HP, 120 Volt (White)



- 3 Speeds for maximum cooling power
- Mount anywhere with the included wall/ ceiling mount
- Suitable for outdoor use and damp locations
- 1-year limited warranty

Product Description

Great for spaces with or without air conditioning, this wall/ceiling fan can take the edge off of your monthly energy bill by allowing you to use the A/C more sparingly. And with our efficient direct drive design, you'll conserve even more electricity. It also has three speed settings and features a heavy-duty, all-metal construction, and wall/ceiling mount. Whether it's a warehouse, garage, barn, or a crowded summer gathering. ***Master – built for power.***



©2026 Pinnacle Climate Technologies

Features and Benefits

- Great for garages, barns, or workshops, or outside events
- Powerful steel construction
- High airflow for up to 3040 CFM
- 1/6 HP industrial motor
- Mount anywhere with the included wall/ceiling mount
- 3 variable speed settings
- 1-year limited warranty

Key Specs

Model Number	MAC-18WW
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	25
Air Flow (CFM)	3040
Motor Size (HP)	1/3
Variable Speed	Yes
Volts	120
Amps	1
Dimensions (L x W x H) (in.)	22 x 21 x 7

Master is a registered trademark of Pinnacle Climate Technologies, Inc.

©2026 Pinnacle Climate Technologies