

LAKEN

F3636-PBR

Designed to make an impact on large ceilings, Laken features a voluminous architectural shade. The artisanal jute-wrap technique gives the fixture its rich texture and warm color variance. Inside, a pinwheel cluster of lights emits powerful illumination. Laken is finished with Patina Brass metalwork, adding an antiqued quality that complements the rustic nature of the jute.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 21"

Width/Diameter: 35.5"

Length: 35.5"

Minimum Height: 27.75"

Maximum Height: 69.75"

Canopy/Backplate: 6.25"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 13.5lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Natural String

Shade 1 Top Length: 15.75"

Shade 1 Bottom L/W: 15.75" / 0"

Shade 1 Height: 17.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: G25

Max Wattage: 15

Bulb Quantity: 4

Bulb Included: No

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 39" x 39" x 26"

Carton 1 Weight: 20lb

Shipping Method: Truck Only

Country of Origin: VN

