SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



65-635 - Square LED; Wide Beam Angle Canopy Light; 3K/4K/5K CCT Selectable; 60W/75W/90W Wattage Selectable; White Finish

WET LOCATION · DIMMABLE · FC · RoHS COMPLIANT · CCT SELECTABLE · 50,000 HOURS · IP 65 · 0-10V DIMMING

GENERAL

Company	NUVO
EA Height	11.02
EA Width	5.12
EA Length	11.02
Bulb Included	Integrated
Material	Die-cast Aluminum
Fixture Type	Canopy
Product Notes	Multiple half-inch knockouts; Three quarter inch back knockout for pendant applications
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Additional Info	Recommended Mounting Height: 15 to 20 Feet
Amps	0.500-0.217/0.625-0.271/0.750-0.325A
Has Camera	No
Integrated Features	Integrated DC Sensor Port
IOT Enabled	No
Lens Material	Polycarbonate (PC)
Photo Cell	Optional Add-On
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	300W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	190
Color Temp	Warm White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40F to +122F (-40C to +50C)
Lumens	7920L-12557L
Volts	120V-277V
Watts	60W/75W/90W
Max Lumens	12557L
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Square
Mounting Procedure	Ceiling

ADDITIONAL INFO

Warranty	5-Years
Installation Notes	Hinged door for ease of installation

PACKAGING

UPC	045923654183
Case Cube	1.6806
Case Height	11.81
Case Length	21.18
Case Quantity	4
Case UPC	10045923654180
Case Weight	20.68
Case Width	11.61
EA Cube	0.3598
EA Height	11.02
EA Length	11.02
EA Quantity	1
EA Weight	4.73
EA Width	5.12
Pack Type	Brown Box
Web Height	3.62
Web Length	9.57
Web Width	9.57

COMPLIANCE

Bug Rating	B3-U4-G5
CA Prop 65	Lead
DLC ID	S-7KZD81
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026