Project / Job Name:

Location:

Fixture Type:

Notes:



62-8122 - Amalfi; 2-Light 16-Inch LED Vanity; 12 Watt; 3000K/4000K/5000K CCT Selectable; Smoked Graphite; Alabaster Stone Lens

GENERAL

Company	NUVO
EA Height	5.0
EA Width	6.7
EA Length	18.0
Mounting Height	0.75
Mounting Length	14.0
Mounting Width	14.0
Bulb Included	Integrated
Extends (in)	3.25
Material	Aluminum / Steel
Includes	Mounting Strap/Plastic Anchors
Status	Active
Style	Transitional
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	45%
Top To Outlet	8.0
Up Down Installation	Universal
CCT Selectable	Yes
Wattage Selectable	No
Collection	Amalfi
Finish Family	Gray
Amps	0.110A
Lens Finish	Alabaster
Lens Material	Alabaster Stone
Lensed	Yes
Nominal Length	16.0
Power Factor	>0.9
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	32W
Incandescent Equivalent	100W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	30000
Beam Angle (degree)	120
Color Temp	Soft White to Daylight
CRI	90+
Dimming Type	Phase cut
Operating Frequency	60Hz
Operating Temp	-14F to +104F (-10C to +40C)
Lumens	1080L
Volts	120v
Watts	12W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Smoked Graphite
Housing Color	Smoked Graphite
ANSI Base	Integrated
Lamp Type	Integrated LED

ADDITIONAL INFO

Warranty	3-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416927
Case Cube	2.5363
Case Height	16.54
Case Length	18.7
Case Quantity	6
Case UPC	10045923416924
Case Weight	25.3
Case Width	14.17
EA Cube	0.349
EA Height	5.0
EA Length	18.0
EA Quantity	1
EA Weight	3.96
EA Width	6.7
Pack Type	Kraft Box
Web Height	5.0
Web Width	16.0

COMPLIANCE

ADA Compliant	Yes
Air Tight	Yes
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026