



Fibre-Metal®

Type II Non-Vented, Industrial Climbing Helmet with HDPE Shell, 8-Point Textile Suspension, Wheel Ratchet Adjustment and a 4-Point Chinstrap

- Liquid Crystal Polymer (LCP) yarn in the six strap, eight-point suspension disperses force transferred from the shell to the user
- Non-Newtonian foam combined with a traditional EPS foam liner
- One-way moisture transfer and fast-dry chin strap help elevate user comfort in high-temperature work environments, by providing a dry and comfortable feel
- Compatible with a wide range of safety accessories such as a welding helmet, visor, faceshield, UV shade, earmuffs, or task light
- ANSI/CSA Certified, Type II, Class E



Technical Data

Color	Black, Multi, Brown, Dark Blue, Orange, Red, White, Gray, Green, Yellow
Sizes Available	OS
Packaging	Bagged Each
Packed	8/Case
Case Dimensions (in)	22.44 x 17.72 x 19.69
Case Weight (lbs)	14.99
Country of Origin	China
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Micro
Size Adjustment	Wheel Ratchet
Chin Strap	4-Point Polyester
Certifications	ANSI/ISEA Z89.1, EN 12492, CSA Z94.1 Certified

Performance Data

ANSI Type	Type II
Electrical Class	Class E

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
CSH10011	Black	OS	00883940437019		00883940437019
CSH10012	Brown	OS	00883940437002		00883940437002
CSH10071	Dark Blue	OS	00883940436975		00883940436975
CSH10009	Gray	OS	00883940436944		00883940436944
CSH10004	Green	OS	00883940436968		00883940436968
CSH10080	Multi	OS	00883940437026		00883940437026
CSH10046	Orange	OS	00883940436982		00883940436982
CSH10015	Red	OS	00883940436999		00883940436999
CSH10001	White	OS	00883940436937		00883940436937
CSH10002	Yellow	OS	00883940436951		00883940436951