



FF7BK



33.25" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, with flat door liner, automatic defrost operation and black exterior

Highlights:

- ETL-S listed to NSF-7 commercial standards
- Low maintenance operation with automatic defrost
- Ideal 24" compact footprint offers large 5.5 c.f. capacity

Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Automatic defrost	Reduced user maintenance with automatic defrost
One piece seamless interior liner	Enjoy easy clean-up with a one piece liner that won't hold a mess in hidden crevices
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Adjustable thermostat	Dial thermostat located inside for easy temperature management
Interior light on rocker switch	Turn the light on when you need it and off when you're done with a convenient rocker switch located just behind the thermostat
Reversible door	Keep your options flexible with a reversible door that's easy to switch when your arrangement changes
Deep shelf space	Interior accommodates large trays up to 19 1/2" x 15 1/2"



FF7BK Specifications:

Overview	
Nominal Height	33.0" (84 cm)
Height of Cabinet	32.63" (83 cm)
Height to Hinge Cap	33.25" (84 cm)
Nominal Width	24.0" (61 cm)
Width	23.63" (60 cm)
Nominal Depth	24.0" (61 cm)
Depth	23.5" (60 cm)
Depth with Handle	24.63" (63 cm)
Depth with door at 90°	45.13" (115 cm)
Capacity	5.3 cu.ft. (150 L)
Defrost Type	Automatic
Door	Black
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Energy Usage/Year	276.0kWh/year
Amps	0.8
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs. (45 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101067421
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R600a
Refrigerant Amount	0.64oz.
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	27.75" (70 cm)
Interior Width	20.0" (51 cm)

Interior Depth	17.5" (44 cm)
Compressor Step Height	7.0" (18 cm)
Compressor Step Width	20.0" (51 cm)
Compressor Step Depth	6.0" (15 cm)

