PRODUCT INFORMATION PACKET

Model No: A134
Catalog No: A134
Round Outlet Shaded Pole OEM Replacement Draft Inducer Blower, 115 Volts, Flange: No
Draft Inducer Blowers



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Voltage	**115 V**	Motor Type	**Shaded Pole**
Thermal Protection	**Thermally**	Speed	**3060 rpm**
Current	**1.5 A**	Number of Speeds	**1**
Frequency	**60 Hz**	Phase	**1**
Ambient Temperature	**40 °C**	UL	**Yes**
Insulation Class	**B**	CSA	**Yes**

Technical Specifications

Blower Outlet Shape	**Round**	Motor Enclosure	**Open**
Blower Outlet Flange	**No**	Bearing Type	**Ball**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021