Jensen | E22082-138BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A tapered, ribbed glass shade adds a contemporary edge to a simple design. Available in Clear Ribbed glass with a plated Gold frame or in Emerald Green or Smoked glass with Matte Black frames. These retro-futuristic shades minimize peripheral glare, while a Matte White acrylic shallow domed diffuser softly disperses LED lighting, delivering ample illumination. The collection includes versatile pendant and flush mount options, with the latter doubling as a wall sconce.



*Height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 11.75" W x 11.75" H x 4" Ext
MAX OAH	: 4.75" W x 4.75" H
HANGING WEIGHT	: 3.53 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,610 Rated (560 Del.)
BULB	: 1 x 21W LED AC Integrated , 21W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black (BK)
Satin Brass (SBR)

GLASS

Smoke 138

MATERIAL

Steel, Glass

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com