



## Technical Data

|                      |                                                   |
|----------------------|---------------------------------------------------|
| Color                | Gray                                              |
| Sizes Available      | 10"-24"                                           |
| Packaging            | Bulk Pack                                         |
| Packed               | 144/Case                                          |
| Case Dimensions (in) | 17.99 x 12.00 x 9.00                              |
| Case Weight (lbs)    | 6.00                                              |
| Country of Origin    | United States                                     |
| Liner Material       | ACP, Dyneema                                      |
| Top of Arm           | Elastic Cuff                                      |
| Ply                  | 2-Ply                                             |
| Construction         | Seamless Knit                                     |
| Certifications       | 21 CFR, Silicone Free, TAA Compliant              |
| Product Circularity  | Reusable / Launderable<br>Recycled via Terracycle |

## Claw Cover®

### 2-Ply ACP / Dyneema® Blended Sleeve

- The proprietary ACP, Dyneema® blend offers superior cut resistance, exceptional comfort and will not cause skin irritation
- Superior washability, can be washed repeatedly in chlorine bleach and caustic detergents or can be dry-cleaned, shrink resistant
- 100% latex and silicone-free
- Complies with FDA food handling requirements 21 CFR, Part 177

## Applications

- High Tensile Strength, Extremely Flexible and Breathable
- Industrial Applications
- Food Processing

## Performance Data

|           |    |
|-----------|----|
| Cut Level | A4 |
|-----------|----|

## Care Instructions



Machine  
Wash



Water Temp  
40°C



Bleach



Tumble Dry



Low Heat

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

**PIP GLOBAL SAFETY | PROTECTION EMPOWERED™**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-12

## SKU Information

| SKU     | COLOR | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|---------|-------|------|--------------|----------------|----------------|
| 20-DA10 | Gray  | 10"  | 616314126215 | 01616314126214 | 02616314126213 |
| 20-DA12 | Gray  | 12"  | 616314126222 | 01616314126221 | 02616314126220 |
| 20-DA14 | Gray  | 14"  | 616314126239 | 01616314126238 | 02616314126237 |
| 20-DA16 | Gray  | 16"  | 616314126246 | 01616314126245 | 02616314126244 |
| 20-DA18 | Gray  | 18"  | 616314126253 | 01616314126252 | 02616314126251 |
| 20-DA20 | Gray  | 20"  | 616314126260 | 01616314126269 | 02616314126268 |
| 20-DA24 | Gray  | 24"  | 616314126277 | 01616314126276 | 02616314126275 |