SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

62-8088 - Maverick; 6-Inch Flush Mount; 12 Watt; 3000K/4000K/5000K CCT Selectable; Gilded Bronze; Light Brown Faux Leather

DAMP LOCATION | 90+ CRI | DIMMABLE | ETL US | FC | RoHS COMPLIANT | CCT SELECTABLE | 30,000 HOURS | 3 YEAR WARRANTY | 120 VOLT

GENERAL

Company	NUVO
EA Height	6.9
EA Width	6.9
EA Length	6.9
Mounting Height	0.75
Bulb Included	Integrated
Diameter	6.0
Material	Aluminum / Steel
Includes	Mounting Strap/Screws/Anchors/Capnuts
Status	Active
Style	Modern and Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	45%
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	No
Collection	Maverick
Finish Family	Bronze
Amps	0.110A
Mounting Diameter	6.0
Lens Finish	Opal
Lens Material	Glass
Lensed	Yes
Power Factor	>0.9
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	32W
Incandescent Equivalent	100W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	30000
Beam Angle (degree)	120
Color Temp	Soft White to Natural Light
CRI	90+
Dimming Type	Phase cut
Operating Frequency	60Hz
Operating Temp	-14F to +104F (-10C to +40C)
Lumens	1080L
Volts	120v
Watts	12W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Gilded Bronze
Housing Color	Gilded Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Cylinder

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923417221
Case Cube	1.8624
Case Height	15.16
Case Length	14.57
Case Quantity	12
Case UPC	10045923417228
Case Weight	21.12
Case Width	14.57
EA Cube	0.1901
EA Height	6.9
EA Length	6.9
EA Quantity	1
EA Weight	2.42
EA Width	6.9
Pack Type	Kraft Box
Web Height	4.75
Web Width	6.0

COMPLIANCE

ADA Compliant	No
Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026