
Alumilux Sideline | E42364-ABZ

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Sleek architectural lines meet flexible performance. The Sideline Outdoor sconce features a wide, flat aluminum profile that casts light along its sides in a continuous glow. Rated for Wet Locations and finished in durable powder-coat finishes that include Matte White, Black, Architectural Bronze, and Satin Aluminum, the Sideline ensures clean, modern styling for any exterior setting. A plated variation in Natural Aged Brass or Polished Chrome brings the same refined silhouette indoors, see Sideline: Bath Vanity.



MEASUREMENTS

DIMENSION	: 51" L 4.75" H x 3" Ext
BACK PLATE	: 4.75" W x 11" H x 25.5" HCO
HANGING WEIGHT	: 6.38 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 4,200 Rated (3,000 Del.)
BULB	: 2 x 30W LED AC Integrated , 60W Total
BULB INCLUDED	: (Integrated)
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Architectural Bronze (ABZ)
Black (BK)

MATERIAL

Aluminum, PC

RATINGS

cETLus
Wet Location
CA Title 24
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com