






PRODUCT DESCRIPTION

A tapered, ribbed glass shade adds a contemporary edge to a simple design. Available in Clear Ribbed glass with a plated Gold frame or in Emerald Green or Smoked glass with Matte Black frames. These retro-futuristic shades minimize peripheral glare, while a Matte White acrylic shallow domed diffuser softly disperses LED lighting, delivering ample illumination. The collection includes versatile pendant and flush mount options, with the latter doubling as a wall sconce.



*max overall height

MEASUREMENTS

DIMENSION	: 18" L x 18" W x 7.5" H
MAX OAH	: 52.75" OAH
CANOPY	: 5.5" W x 0.75" H x 5.5" L
HANGING WEIGHT	: 13.89 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 3,900 Rated (1,260 Del.)
BULB	: 1 x 28W LED AC Integrated , 28W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Satin Brass (SBR)

GLASS

Smoke 138

MATERIAL

Steel, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com