



WORLDWIDE ELECTRIC MOTOR DATA SHEET

WPMDC12-18-90V-56CB



HP	1/2
RPM / POLES	1800 / 4
ARMATURE VOLTAGE	90 V
FRAME	56C
ENCLOSURE	TENV / IP54
ARMATURE FULL LOAD AMPS	5.2 A
FULL LOAD TORQUE	1.46 LB. FT.
FORM FACTOR	1.0
SERVICE FACTOR	1.0
INSULATION CLASS	F
AMBIENT TEMP.	40° C
BASE TYPE	C-FACE - REMOVABLE
SHAFT	KEYED
DE BEARING	6203
ODE BEARING	6203
MOUNTING	F3
ROTATION	CW / CCW
WIRE TYPE	LOOSE WIRE
WIRE HOUSING	JUNCTION BOX
APPROX. WEIGHT	22 LBS.
FL EFFICIENCY	82.0%



REVISED - 07/25/16

KEY		KEYSEAT		FLANGE			SHAFT		
AH	BC	ES	S	R	AJ	AK	BF	N-W	U
2.06	0.12	1.41	0.188	0.517	5.875	4.5	3/8-16	1.88	0.625

ALL DIMENSIONS IN INCHES