



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**TH762** - 8 Watt LED Track Head;  
 2700K/3000K/3500K/4000K/5000K CCT Selectable; Dim to Warm;  
 H Style; 36 Degree Beam Angle; 120 Volt; Black; Round



GENERAL	
Company	SATCO
EA Height	5.31
EA Width	2.68
EA Length	2.95
Mounting Height	4.25
Mounting Length	2.25
Mounting Width	2.25
Bulb Included	Integrated
Center Beam Candle Power	900
Diameter	2.28
Dimmable Text	Forward or Reverse Phase; 120V only
Extends (in)	5.0
Material	Aluminum
Fixture Type	Track Head
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	<100%
Track Head Style	Round
Up Down Installation	Universal
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	Black
Amps	0.070A
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Power Factor	>0.92
SDS Class	LED_Fixture
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	11W
Incandescent Equivalent	40W

ELECTRICAL	
CCT (Kelvin Temp)	2700K/3000K/3500K/4000K/5000K/3000K-2000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	36
Color Temp	Warm Dimming, Warm White to Natural Light
CRI	90+
Dimming Type	120V only, Phase cut
Operating Frequency	60Hz
Operating Temp	-20C (-4F) to +40C (+104F)
Lumens	500L-600L
Volts	120v
Watts	8W

PHYSICAL	
Lamp Base	Integrated
Finish	BLACK
Housing Color	Black
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO	
Warranty	3-Years

FEATURES	
Flicker Free	Yes

PACKAGING	
UPC	045923412332
Case Cube	0.7238
Case Height	11.42
Case Length	16.85
Case Quantity	24
Case UPC	10045923412339
Case Weight	13.44
Case Width	6.5
EA Cube	0.0243
EA Height	5.31
EA Length	2.95
EA Quantity	1
EA Weight	0.56
EA Width	2.68
Pack Type	Kraft Box
Web Length	2.87

COMPLIANCE	
ADA Compliant	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
Location Rating	Dry
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Title 20	Exempt
T24 Compliant	Yes